



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NHC1023CR 90 Male Cord Conn, .38-.50", 1/2", Nyl, G *Hubbell Wiring Devices*

Catalog Number	NHC1023CR
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Cord Connectors, 90 Degree Male .38-.50", 1/2", Nylon
Weight per unit	0.1000 (lbs/each)
Product Category	Cable & Cord Grips

Features

Material	Nylon
Number of Conductors	Single
pallet quantity	7875

Material, Color, and Finish

Color	Gray
Color Code	BLUE

Dimensions and Weight

Size	1/2" NPT
------	----------

Descriptions

Description	90 MALE CORD CONN, .38-.50", 1/2", NYL,G
extra long description	HWDK NHC1023CR 90 MALE CORD CONN, .
Features	Cord Connectors - Hubbell has the broadest line and the widest choice of materials in the industry. NPT hub sizes from 1/4" to 3" in straight male end, 90°, 45°, female and underground feed connectors. They are available in your choice of aluminum, plated steel, nylon and stainless steel. The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and oth
Long Description	Kellems Wire Management, Cord Connectors, 90 Degree Male .38-.50", 1/2", Nylon
Product Type	90 Male Cord Conn, .38-.50", 1/2", Nyl, G
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585208756
Manufacturers Part Number	NHC1023CR
series	Standard Duty
UPC	783585208756



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	90° Male

Packaging

Carton	1
Package	25
Weight Per each	0.1

Uses, Certifications, and Standards

Application	90 Degree Male- Form 2
environmental conditions	Suitable for use in wet locations when used with a listed nylon washer between box and fitting.
Mounting	Locknut or Tapped Opening
nema rating	12;4;4X;NEMA Type 4, 4X, 12 and 13
standard	UL Listed
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)