



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NK2FIWY 2P Single Gang Faceplate

Panduit Corporation

| | |
|------------------|---|
| Catalog Number | NK2FIWY |
| Manufacturer | Panduit Corporation |
| Description | The Netkey® Faceplate Accepts Two Keystone Modules. The Faceplate Is Single Gang and Mounts to A Nema Standard Single Gang Opening. The Faceplate Includes A Label Pocket For Easy Identification and Is Off White. |
| Weight per unit | 0.0500 (lbs/each) |
| Product Category | Wiring Devices |

Features

| | |
|----------|-----|
| Material | ABS |
|----------|-----|

Material, Color, and Finish

| | |
|-------|-----------|
| Color | Off White |
|-------|-----------|

Dimensions and Weight

| | |
|-------|------|
| Depth | 0.45 |
| Width | 2.75 |

Descriptions

| | |
|------------------------|---|
| Description | 2P SINGLE GANG FACEPLATE |
| extra long description | PAN NK2FIWY NetKey® Faceplate, Labe |
| Long Description | The NetKey® Faceplate accepts two keystone modules. The faceplate is single gang and mounts to a NEMA standard single gang opening. The faceplate includes a label pocket for easy identification and is off white. |
| Product Type | Netkey® Faceplate, Label Pocket, 2 Port, Off White |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983054527 |
| Manufacturers Part Number | NK2FIWY |
| Model | Keystone |
| UPC | 074983054527 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | FACEPLATE |

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 0.05 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|----------------|
| Application | NA |
| standard | RoHS Compliant |