



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## P1014RD Pan-Term® P10-14R-D Ring *Panduit Corporation*

Catalog Number	P1014RD
Manufacturer	Panduit Corporation
Description	The P10-14R-D Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0046 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Standard
insulation	None
Material	Copper
media	Yes
Voltage Rating	2000
Wire Size	#10

### Material, Color, and Finish

Finish	Tinned
--------	--------

### Dimensions and Weight

Size	1/4"
------	------

### Descriptions

Description	PAN-TERM® P10-14R-D RING
extra long description	PAN P10-14R-D Pan-Term® P10-14R-D R
Long Description	The P10-14R-D Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® P10-14R-D Ring Terminal, Bare, 10-14 Awg, 1/4" Stu

### Manufacturer Information

Brand	Panduit®
GTIN	00074983802357
Manufacturers Part Number	P10-14R-D
UPC	074983802357

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton .....	500 .....
Weight Per each .....	0.0046 .....

## Uses, Certifications, and Standards

Enclosure .....	Ring shape .....
Mounting .....	9/32 .....
standard .....	UL Listed 587H E52164, CSA Certified LR31212 .....
Temperature Rating .....	302 Degrees Fahrenheit (150 Degrees Celsius) .....