



P-181



P-181RK



P-201QT



P-201R



P-122SC



P-241



\*Quick Thread™ device hole

| Nail-On | Cu. In. Volume | Catalog Number | Component Description  | Exterior Dimensions |                        |       | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|---------|----------------|----------------|--|---------------------|------------------------|-------|------------|----------------|----------------|
|         |                |                |  | D                   | W                      | H     |            |                |                |
|         | 18.0           | P-181          | Single gang, angled mid-nails  | 2-5/8               | 2-5/16                 | 3-3/4 | 24391      | 100            | 21             |
|         | 18.0           | P-181QT        | Single gang, angled mid-nails, Quick Thread™ device holes                                      | 2-5/8               | 2-5/16                 | 3-3/4 | 24399      | 100            | 21             |
|         | 18.0           | P-181RK        | Single gang, reverse nails, molded-in Speed Klamps™  | 2-11/16             | 2-5/16                 | 3-3/4 | 24398      | 100            | 21             |
|         | 20.5           | P-201          | Single gang, angled nails  | 3-1/16              | 2-5/16                 | 3-3/4 | 24900      | 100            | 23             |
|         | 20.5           | P-201QT        | Single gang, angled nails, Quick Thread™ device holes  | 3-1/8               | 2-5/16                 | 3-3/4 | 24909      | 100            | 25             |
|         | 20.5           | P-201R         | Single gang, reverse nails   | 3-1/16              | 2-5/16                 | 3-3/4 | 24901      | 100            | 24             |
|         | 23.5           | P-122SC        | Patented single gang with side cube, angled mid-nails, four wire knockouts, 2 recessed buttons | 1-3/4               | 2-9/32 (5-1/2 overall) | 3-3/4 | 24914      | 24             | 9              |
|         | 24.0           | P-241          | Single gang, angled nails  | 3-9/16              | 2-5/16                 | 3-3/4 | 24903      | 100            | 26             |
|         | 24.0           | P-241QT        | Single gang, angled nails, Quick Thread™ device holes  | 3-9/16              | 2-5/16                 | 3-3/4 | 24904      | 100            | 27             |



P-181H



P-181HZ



P-241H



P-241HQT



P-108E



P-108H



P-1160W



P-1180W



P-1220W

| Face Bracket Mount | Cu. In. Volume | Catalog Number | Component Description  | Exterior Dimensions |        |       | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|--------------------|----------------|----------------|--|---------------------|--------|-------|------------|----------------|----------------|
|                    |                |                |  | D                   | W      | H     |            |                |                |
|                    | 18.0           | P-181H         | Single gang, face bracket mount, 1/2" NM knockouts             | 2-3/4               | 2-5/16 | 3-3/4 | 24916      | 48             | 10             |
|                    | 18.0           | P-181HZ        | Single gang, face bracket mount, 1/2" NM knockouts, "Z" hanger | 2-3/4               | 2-5/16 | 3-3/4 | 24919      | 36             | 11             |
|                    | 24.0           | P-241H         | Single gang, face bracket mount                                | 3-9/16              | 2-5/16 | 3-3/4 | 24907      | 50             | 12             |
|                    | 24.0           | P-241HQT       | Single gang, face bracket mount, Quick Thread™ device holes    | 3-9/16              | 2-5/16 | 3-3/4 | 24908      | 50             | 12             |

| Miscellaneous | Cu. In. Volume | Catalog Number | Component Description   | Exterior Dimensions |        |         | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|---------------|----------------|----------------|---|---------------------|--------|---------|------------|----------------|----------------|
|               |                |                |   | D                   | W      | H       |            |                |                |
|               | 8.0            | P-108E         | Single gang, ears   | 1-1/4               | 2-5/16 | 3-3/4   | 24917      | 24             | 3              |
|               | 8.0            | P-108H         | Single gang, side bracket mount   | 1-1/4               | 2-5/16 | 3-3/4   | 24918      | 24             | 3              |
|               | 16.0           | P-1160W        | Single gang, ears, wing brackets, 1/2" NM knockouts                         | 2-5/8               | 2-5/16 | 3-11/16 | 24915      | 48             | 10             |
|               | 18.0           | P-1180W        | Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout | 3                   | 2-1/4  | 3-11/16 | 92714      | 48             | 11             |
|               | 22.5           | P-1220W        | Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout | 3-3/4               | 2-5/16 | 3-3/4   | 24913      | 48             | 14             |

All dimensions are in inches unless otherwise noted.

See page 32 for flexbox® Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Flush-Device Box  
UL File No. E30594



\*Quick Thread™ device hole



Nail-On

| Cu. In. Volume | Catalog Number | Component Description  | Exterior Dimensions |                        |       | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------|----------------|--|---------------------|------------------------|-------|------------|----------------|----------------|
|                |                |  | D                   | W                      | H     |            |                |                |
| 18.0           | P-181          | Single gang, angled mid-nails  | 2-5/8               | 2-5/16                 | 3-3/4 | 24391      | 100            | 21             |
| 18.0           | P-181QT        | Single gang, angled mid-nails, Quick Thread™ device holes                                      | 2-5/8               | 2-5/16                 | 3-3/4 | 24399      | 100            | 21             |
| 18.0           | P-181RK        | Single gang, reverse nails, molded-in Speed Klamps™  | 2-11/16             | 2-5/16                 | 3-3/4 | 24398      | 100            | 21             |
| 20.5           | P-201          | Single gang, angled nails  | 3-1/16              | 2-5/16                 | 3-3/4 | 24900      | 100            | 23             |
| 20.5           | P-201QT        | Single gang, angled nails, Quick Thread™ device holes  | 3-1/8               | 2-5/16                 | 3-3/4 | 24909      | 100            | 25             |
| 20.5           | P-201R         | Single gang, reverse nails   | 3-1/16              | 2-5/16                 | 3-3/4 | 24901      | 100            | 24             |
| 23.5           | P-122SC        | Patented single gang with side cube, angled mid-nails, four wire knockouts, 2 recessed buttons | 1-3/4               | 2-9/32 (5-1/2 overall) | 3-3/4 | 24914      | 24             | 9              |
| 24.0           | P-241          | Single gang, angled nails  | 3-9/16              | 2-5/16                 | 3-3/4 | 24903      | 100            | 26             |
| 24.0           | P-241QT        | Single gang, angled nails, Quick Thread™ device holes  | 3-9/16              | 2-5/16                 | 3-3/4 | 24904      | 100            | 27             |



Face Bracket Mount

| Cu. In. Volume | Catalog Number | Component Description  | Exterior Dimensions |        |       | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------|----------------|--|---------------------|--------|-------|------------|----------------|----------------|
|                |                |  | D                   | W      | H     |            |                |                |
| 18.0           | P-181H         | Single gang, face bracket mount, 1/2" NM knockouts             | 2-3/4               | 2-5/16 | 3-3/4 | 24916      | 48             | 10             |
| 18.0           | P-181HZ        | Single gang, face bracket mount, 1/2" NM knockouts, "Z" hanger | 2-3/4               | 2-5/16 | 3-3/4 | 24919      | 36             | 11             |
| 24.0           | P-241H         | Single gang, face bracket mount                                | 3-9/16              | 2-5/16 | 3-3/4 | 24907      | 50             | 12             |
| 24.0           | P-241HQT       | Single gang, face bracket mount, Quick Thread™ device holes    | 3-9/16              | 2-5/16 | 3-3/4 | 24908      | 50             | 12             |

Miscellaneous

| Cu. In. Volume | Catalog Number | Component Description   | Exterior Dimensions |        |         | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------|----------------|---|---------------------|--------|---------|------------|----------------|----------------|
|                |                |   | D                   | W      | H       |            |                |                |
| 8.0            | P-108E         | Single gang, ears   | 1-1/4               | 2-5/16 | 3-3/4   | 24917      | 24             | 3              |
| 8.0            | P-108H         | Single gang, side bracket mount   | 1-1/4               | 2-5/16 | 3-3/4   | 24918      | 24             | 3              |
| 16.0           | P-1160W        | Single gang, ears, wing brackets, 1/2" NM knockouts                         | 2-5/8               | 2-5/16 | 3-11/16 | 24915      | 48             | 10             |
| 18.0           | P-1180W        | Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout | 3                   | 2-1/4  | 3-11/16 | 92714      | 48             | 11             |
| 22.5           | P-1220W        | Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout | 3-3/4               | 2-5/16 | 3-3/4   | 24913      | 48             | 14             |

All dimensions are in inches unless otherwise noted.  
See page 32 for flexbox® Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Flush-Device Box  
UL File No. E30594