

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3817-09

Melon

Two-light close-to-ceiling with etched ribbed melon glass with center lock up in Brushed Nickel finish.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched ribbed glass bowl



Diameter: 13-1/4"

Height: 7"

Glass: 9-13/16" dia.

Height: 4-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" hexagonal recessed outlet box 13-1/4" dia., 1-5/8"	Pre-wired 6" of wire supplied 120V	Quantity: 2 75W Medium Base Medium sockets	cCSAus Damp location listed 1 year warranty Companion fixtures are available

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3817-09

Melon

Two-light close-to-ceiling with etched ribbed melon glass with center lock up in Brushed Nickel finish.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched ribbed glass bowl



Diameter: 13-1/4"

Height: 7"

Glass: 9-13/16" dia.

Height: 4-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" hexagonal recessed outlet box 13-1/4" dia., 1-5/8"	Pre-wired 6" of wire supplied 120V	Quantity: 2 75W Medium Base Medium sockets	cCSAus Damp location listed 1 year warranty Companion fixtures are available