

# Eaton P48G11S03P

Catalog Number: P48G11S03P

Eaton Mini-Power Center, Single-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 120/240V, 115°C, 3 kVA, Al windings , Frame: 283, Indoor-Outdoor.



Photo is representative

## General specifications

### Product Name

Eaton Mini-Power center

### Catalog Number

P48G11S03P

### UPC

786680140136

### Product Length/Depth

8.9 in

### Product Height

27.5 in

### Product Width

11.9 in

### Product Weight

130 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

NEMA Compliant

### Certifications

UL Listed  
ANSI  
CSA Certified  
IEEE Certified

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

283

### Tap size

2 at -5% FCBN

### Type

Mini-power center

### Wiring connection

97A3K

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

3 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - P48G11S03P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)