

# Specifications

Photo is representative



## Eaton P48G11S03P

Eaton Mini-Power Center,  
Single-phase, PV: 480V,  
Taps: 2 at -5% FCBN, SV:  
120/240V, 115°C, 3 kVA,  
Al windings , Frame: 283,  
Indoor-Outdoor.

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>ENCLOSURE</b>	NEMA 3R
<b>FRAME</b>	283
<b>TAP SIZE</b>	2 at -5% FCBN
<b>TYPE</b>	Mini-power center
<b>WIRING CONNECTION</b>	97A3K

### General specifications

<b>PRODUCT NAME</b>	Eaton Mini-Power center
<b>CATALOG NUMBER</b>	P48G11S03P
<b>UPC</b>	786680140136
<b>PRODUCT LENGTH/DEPTH</b>	8.9 in
<b>PRODUCT HEIGHT</b>	27.5 in
<b>PRODUCT WIDTH</b>	11.9 in
<b>PRODUCT WEIGHT</b>	130 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	NEMA Compliant
<b>CERTIFICATIONS</b>	UL Listed ANSI CSA Certified IEEE Certified