

Eaton P48G11S0512

Catalog Number: P48G11S0512

5 KVA Mini Power Center 1PH 480V-120/240V 12 spaces



Photo is representative

General specifications

Product Name

Eaton Mini-Power center

Catalog Number

P48G11S0512

UPC

786680225536

Product Length/Depth

8.9 in

Product Height

29.5 in

Product Width

11.9 in

Product Weight

167 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

NAFTA

Certifications

CSA Certified

UL Listed

ANSI

IEEE Certified

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 3R

Frame

284

Insulation

180 °C

Mounting

Wall Mount

Tap size

2 at -5% FCBN

Type

Mini-power center

Wiring connection

M48G11D

Performance Ratings

Frequency rating

60 Hz

kVA

5 kVA

Kva Rating

5 kVA

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Modification 1

NEMA 3R

Weathershield

Not required

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - P48G11S0512](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)