

Specifications

Photo is representative



Eaton P48G11S05P

Eaton Mini-Power Center,
Single-phase, PV: 480V,
Taps: 2 at -5% FCBN, SV:
120/240V, 115°C, 5 kVA,
Al windings , Indoor-
Outdoor.B45, Frame: 284

Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	284
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	110A5K

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S05P
UPC	786680140204
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	16 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	146 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed IEEE Certified CSA Certified ANSI

Specifications

Photo is representative



Eaton P48G11S05P

Eaton Mini-Power Center,
Single-phase, PV: 480V,
Taps: 2 at -5% FCBN, SV:
120/240V, 115°C, 5 kVA,
Al windings , Indoor-
Outdoor.B45, Frame: 284

Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	284
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	110A5K

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S05P
UPC	786680140204
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	16 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	146 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed IEEE Certified CSA Certified ANSI