

# Eaton P48G11S15P

Catalog Number: P48G11S15P

Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K



## General specifications

### Product Name

Eaton Mini-Power center

### Catalog Number

P48G11S15P

### UPC

786680140228

### Product Length/Depth

11.6 in

### Product Height

37.5 in

### Product Width

13.1 in

### Product Weight

232 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

NEMA Compliant

### Certifications

ANSI

IEEE Certified

UL Listed

CSA Certified

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

286

### Tap size

2 at -5% FCBN

### Type

Mini-power center

### Wiring connection

107A15K

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - P48G11S15P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton P48G11S15P

Catalog Number: P48G11S15P

Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K



## General specifications

### Product Name

Eaton Mini-Power center

### Catalog Number

P48G11S15P

### UPC

786680140228

### Product Length/Depth

11.6 in

### Product Height

37.5 in

### Product Width

13.1 in

### Product Weight

232 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

NEMA Compliant

### Certifications

ANSI

IEEE Certified

UL Listed

CSA Certified



Powering Business Worldwide

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

286

### Tap size

2 at -5% FCBN

### Type

Mini-power center

### Wiring connection

107A15K

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - P48G11S15P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)