

Eaton P48G11S15P

Catalog Number: P48G11S15P

Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K



General specifications

Product Name

Eaton Mini-Power center

Catalog Number

P48G11S15P

UPC

786680140228

Product Length/Depth

11.6 in

Product Height

37.5 in

Product Width

13.1 in

Product Weight

232 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

NEMA Compliant

Certifications

ANSI

IEEE Certified

UL Listed

CSA Certified

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 3R

Frame

286

Tap size

2 at -5% FCBN

Type

Mini-power center

Wiring connection

107A15K

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - P48G11S15P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)