

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500241-009 Clarion

Who says you have to sacrifice forms for function? This versatile pendant features a simple, clear glass shade that embraces minimalist modernity and functional task lighting. The glass shade rests at the end of a sleek brushed nickel bar that attaches to the ceiling. Each light fixture has a swivel at its base that makes it perfect for installing on flat or angled ceilings.

- This versatile pendant features a simple, clear glass shade that embraces minimalist modernity and functional task lighting.
- The glass shade rests at the end of a sleek brushed nickel bar that attaches to the ceiling.
- Each light fixture has a swivel at its base that makes it perfect for installing on flat or angled ceilings.
- Ideal for any foyer, dining room, or kitchen.
- Perfect for transitional, modern, farmhouse, coastal, contemporary, and luxury settings.
- Measures 9-inch width by 11-3/8-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear glass Cone shaped shade



Diameter: 9 in
Height: 11-3/8 in
Overall Ht. W/Stem: 67-1/2 in

Clear glass Cone shaped shade
Width: 9 in
Height: 10-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity: One 60 W max. Medium Base or LED equivalent	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	E26 base Porcelain socket	1-year Limited Warranty
One 6", four 12" lengths of stem included	120 V		
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.875" ht., 2.125" depth			