



DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

## P5683-31

### Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light wall lantern.

**Category:** Outdoor

**Finish:** Textured Black (painted)

**Construction:** Die-cast aluminum construction

**Glass:** Clear beveled glass panels



**Width:** 9-3/8"

**Height:** 16"

**Depth:** 11-1/4"

**H/CTR:** 3-1/2"

**Glass:** 3-3/4" Top, 2-5/16" Bottom

**Height:** 7-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting strap for outlet box included  Back plate covers a standard 4" hexagonal recessed outlet box  4-1/2", 7"ht.	Pre-wired  6" of wire supplied  120V	Quantity: 1 100W Medium Base  Medium ceramic socket	UL-CUL Wet location listed  1 year warranty  Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available



DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

## P5683-31

### Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light wall lantern.

**Category:** Outdoor

**Finish:** Textured Black (painted)

**Construction:** Die-cast aluminum construction

**Glass:** Clear beveled glass panels



**Width:** 9-3/8"

**Height:** 16"

**Depth:** 11-1/4"

**H/CTR:** 3-1/2"

**Glass:** 3-3/4" Top, 2-5/16" Bottom

**Height:** 7-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting strap for outlet box included  Back plate covers a standard 4" hexagonal recessed outlet box  4-1/2", 7"ht.	Pre-wired  6" of wire supplied  120V	Quantity: 1 100W Medium Base  Medium ceramic socket	UL-CUL Wet location listed  1 year warranty  Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available