



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P614RT Pan-Term® P6-14R-T Ring T *Panduit Corporation*

Catalog Number	P614RT
Manufacturer	Panduit Corporation
Description	The P6-14R-T Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0092 (lbs/each)
Product Category	Large Terminals & Connectors

Features

connection	Standard
media	Yes
Voltage Rating	2000

Descriptions

Description	PAN-TERM® P6-14R-T RING T
extra long description	PAN P6-14R-T Pan-Term® P6-14R-T Rin
Long Description	The P6-14R-T Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® P6-14R-T Ring Terminal, Bare, 6 Awg, 1/4" Stud, PK

Manufacturer Information

Brand	Panduit®
GTIN	00074983870738
Manufacturers Part Number	P6-14R-T
UPC	074983870738

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Packaging

Carton	200
Weight Per each	0.0092

Uses, Certifications, and Standards

Enclosure	Ring shape
Temperature Rating	302 Degrees Fahrenheit (150 Degrees Celsius)