

PVC Coated Strut Straps and J Hangers

Plasti-Bond PVC coated strut straps & J hangers are used with coated strut to support conduit installations in a variety of configurations. Strut straps may be used in either vertical or horizontal positions to support conduit. Both are provided with stainless steel hardware. Conduit spacing may be as close together as allowed by the couplings. J hangers may be used with hanger rods or other means of support to securely fasten conduit runs.

Features:

- 20 mil gray PVC exterior coating
- Available in 11 trade sizes



J Hanger



Strut Straps

PVC COATED J HANGERS

SIZE	FERROUS CATALOG #	WEIGHT FOR 100 PCS	STD PACK
1/2"	PBC149-1/2	18	25
3/4"	PBC149-3/4	21	25
1"	PBC149-1	22	25
1-1/4"	PBC149-1-1/4	25	25
1-1/2"	PBC149-1-1/2	27	25
2"	PBC149-2	29	25
2-1/2"	PBC149-2-1/2	64	25
3"	PBC149-3	72	25
3-1/2"	PBC149-3-1/2	84	25
4"	PBC149-4	138	10
5"	PBC149-5	162	10

PVC COATED STRUT STRAPS


SIZE	FERROUS CATALOG #	GAUGE METAL	WEIGHT FOR 100 PCS	STD PACK
1/2"	PBC105-1/2	14	13.0	100
3/4"	PBC105-3/4	14	15.0	100
1"	PBC105-1	14	17.0	100
1-1/4"	PBC105-1-1/4	12	19.5	100
1-1/2"	PBC105-1-1/2	12	28.0	100
2"	PBC105-2	12	31.0	50
2-1/2"	PBC105-2-1/2	12	36.0	50
3"	PBC105-3	12	42.0	50
3-1/2"	PBC105-3-1/2	11	56.0	25
4"	PBC105-4	11	64.0	25
5"	PBC105-5	10	76.0	25

PVC Coated Ferrous Struts

Plasti-Bond PVC coated strut is a versatile system of structural elements that can be used to build supports for a variety of applications. When combined with coated conduit hangers and other accessories, coated strut is a versatile and economical way to provide reliable support for conduit runs and other electrical and mechanical installations.

Features:

- 20 mil gray PVC exterior coating
- 2 trade sizes and 3 standard styles



PVC COATED STRUT

FERROUS CATALOG #	STYLE	NOMINAL WT. PER 100 FT.	X	Y	STRUT THICKNESS
PBP1000-10	Channel	200.0	1.67	1.67	12 ga.
PBSH1000-10	Channel Slotted	185.0	1.67	1.67	12 ga.
PBP1001-10	Channel Back to Back	380.0	1.67	3.29	12 ga.
PBP3300-10	Channel Shallow	135.0	1.67	0.92	12 ga.
PBSH3300-10	Channel Shallow Slotted	130.0	1.67	0.92	12 ga.

PVC COATED STRUT CUT-TO-LENGTH

FERROUS CATALOG #	DESCRIPTION	X	Y	LENGTH IN FT.	STRUT THICKNESS
PBP1000-1	1-5/8 CHANNEL	1.67	1.67	1	12 ga.
PBP1000-1-1/2	1-5/8 CHANNEL	1.67	1.67	1-1/2	12 ga.
PBP1000-2	1-5/8 CHANNEL	1.67	1.67	2	12 ga.
PBP1000-2-1/2	1-5/8 CHANNEL	1.67	1.67	2-1/2	12 ga.
PBP1000-3	1-5/8 CHANNEL	1.67	1.67	3	12 ga.

CHANNELS WITH SLOTTED HOLES

PBSH1000-1	1-5/8 CHANNEL	1.67	1.67	1	12 ga.
PBSH1000-1-1/2	1-5/8 CHANNEL	1.67	1.67	1-1/2	12 ga.
PBSH1000-2	1-5/8 CHANNEL	1.67	1.67	2	12 ga.
PBSH1000-2-1/2	1-5/8 CHANNEL	1.67	1.67	2-1/2	12 ga.
PBSH1000-3	1-5/8 CHANNEL	1.67	1.67	3	12 ga.

PVC Coated Strut Nuts

Plasti-Bond PVC coated strut nuts are used to assemble strut components and to secure coated all thread rod in a section of strut. These are available with or without a spring to aid in placement and assembly.

Features:


- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



PBB910



PBB911



PBB914

COATED STRUT NUT

PIPE SIZE	FERROUS CATALOG #
3/8"	PBB910-3/8
1/2"	PBB910-1/2
3/8"	PBB911-3/8
1/2"	PBB911-1/2
3/8"	PBB914-3/8
1/2"	PBB914-1/2

PVC Coated Strut Straps and J Hangers

Plasti-Bond PVC coated strut straps & J hangers are used with coated strut to support conduit installations in a variety of configurations. Strut straps may be used in either vertical or horizontal positions to support conduit. Both are provided with stainless steel hardware. Conduit spacing may be as close together as allowed by the couplings. J hangers may be used with hanger rods or other means of support to securely fasten conduit runs.

Features:

- 20 mil gray PVC exterior coating
- Available in 11 trade sizes



J Hanger

Strut Straps

PVC COATED J HANGERS

SIZE	FERROUS CATALOG #	WEIGHT FOR 100 PCS	STD PACK
1/2"	PBC149-1/2	18	25
3/4"	PBC149-3/4	21	25
1"	PBC149-1	22	25
1-1/4"	PBC149-1-1/4	25	25
1-1/2"	PBC149-1-1/2	27	25
2"	PBC149-2	29	25
2-1/2"	PBC149-2-1/2	64	25
3"	PBC149-3	72	25
3-1/2"	PBC149-3-1/2	84	25
4"	PBC149-4	138	10
5"	PBC149-5	162	10

PVC COATED STRUT STRAPS

SIZE	FERROUS CATALOG #	GAUGE METAL	WEIGHT FOR 100 PCS	STD PACK
1/2"	PBC105-1/2	14	13.0	100
3/4"	PBC105-3/4	14	15.0	100
1"	PBC105-1	14	17.0	100
1-1/4"	PBC105-1-1/4	12	19.5	100
1-1/2"	PBC105-1-1/2	12	28.0	100
2"	PBC105-2	12	31.0	50
2-1/2"	PBC105-2-1/2	12	36.0	50
3"	PBC105-3	12	42.0	50
3-1/2"	PBC105-3-1/2	11	56.0	25
4"	PBC105-4	11	64.0	25
5"	PBC105-5	10	76.0	25

PVC Coated Ferrous Struts

Plasti-Bond PVC coated strut is a versatile system of structural elements that can be used to build supports for a variety of applications. When combined with coated conduit hangers and other accessories, coated strut is a versatile and economical way to provide reliable support for conduit runs and other electrical and mechanical installations.

Features:

- 20 mil gray PVC exterior coating
- 2 trade sizes and 3 standard styles




P1001

P1000

SH1000

P3300

SH3300



PVC COATED STRUT

FERROUS CATALOG #	STYLE	NOMINAL WT. PER 100 FT.	X	Y	STRUT THICKNESS
PBP1000-10	Channel	200.0	1.67	1.67	12 ga.
PBSH1000-10	Channel Slotted	185.0	1.67	1.67	12 ga.
PBP1001-10	Channel Back to Back	380.0	1.67	3.29	12 ga.
PBP3300-10	Channel Shallow	135.0	1.67	0.92	12 ga.
PBSH3300-10	Channel Shallow Slotted	130.0	1.67	0.92	12 ga.

PVC COATED STRUT CUT-TO-LENGTH

FERROUS CATALOG #	DESCRIPTION	X	Y	LENGTH IN FT.	STRUT THICKNESS
PBP1000-1	1-5/8 CHANNEL	1.67	1.67	1	12 ga.
PBP1000-1-1/2	1-5/8 CHANNEL	1.67	1.67	1-1/2	12 ga.
PBP1000-2	1-5/8 CHANNEL	1.67	1.67	2	12 ga.
PBP1000-2-1/2	1-5/8 CHANNEL	1.67	1.67	2-1/2	12 ga.
PBP1000-3	1-5/8 CHANNEL	1.67	1.67	3	12 ga.

CHANNELS WITH SLOTTED HOLES

PBSH1000-1	1-5/8 CHANNEL	1.67	1.67	1	12 ga.
PBSH1000-1-1/2	1-5/8 CHANNEL	1.67	1.67	1-1/2	12 ga.
PBSH1000-2	1-5/8 CHANNEL	1.67	1.67	2	12 ga.
PBSH1000-2-1/2	1-5/8 CHANNEL	1.67	1.67	2-1/2	12 ga.
PBSH1000-3	1-5/8 CHANNEL	1.67	1.67	3	12 ga.

PVC Coated Strut Nuts

Plasti-Bond PVC coated strut nuts are used to assemble strut components and to secure coated all thread rod in a section of strut. These are available with or without a spring to aid in placement and assembly.

Features:


- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



PBB910



PBB911



PBB914

COATED STRUT NUT

PIPE SIZE	FERROUS CATALOG #
3/8"	PBB910-3/8
1/2"	PBB910-1/2
3/8"	PBB911-3/8
1/2"	PBB911-1/2
3/8"	PBB914-3/8
1/2"	PBB914-1/2