

4" Dia. Round Outlet:

Residential Units

Series PC234-24



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
23.0	PC234-24	24" adj. bar hanger, molded-in Speed Klamps™	2-3/8	4	50 lb.	98017	50	35
23.0	PC234-24G*	24" adj. bar hanger, ground strap, molded-in Speed Klamps™	2-3/8	4	50 lb.	98018	50	36

Series PC234-N



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
23.0	PC234-N	Angled Fetter ring nails, molded-in Speed Klamps™	2-3/8	4	50 lb.	98025	50	12
23.0	PC234-NG*	Angled Fetter ring nails, ground strap, molded-in Speed Klamps™	2-3/8	4	50 lb.	98026	50	13

Series PC234-UB



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
23.0	PC234-UB	16"-24" universal bar hanger, molded-in Speed Klamps™	2-3/8	4	50 lb.	98015	50	35
23.0	PC234-UBG*	16"-24" universal bar hanger, ground strap, molded-in Speed Klamps™	2-3/8	4	50 lb.	98016	50	36



* Indicates model shown • See page 32 for Attachment Coding descriptions

