

Eaton PDG23G0060TFFL

Catalog Number: PDG23G0060TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 60A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Power Defense molded case circuit breaker	PDG23G0060TFFL
	UPC
	786679911693
Product Length/Depth	Product Height
88.9 mm	152.4 mm
Product Width	Product Weight
104.6 mm	1.82 kg
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	IEC 60947-2
	CSA
	UL 489
	CCC Marked

Delivery program

Amperage Rating

60 A

Circuit breaker frame type

Complete breaker

Frame

2

Number of poles

Three-pole

General information

Circuit breaker type

PD2 Global

Class

Class A

Trip Type

T-M (Fxd-Fxd) TU

Technical data - Electrical

Voltage rating

600 Vac

Voltage rating - max

600 V

Technical data - Mechanical - Terminals

Terminals

Standard Terminals Load Only

Technical information

Interrupt rating

35 kAIC at 480 Vac

Interrupt rating range

36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)

18 kAIC @600V (UL/CSA)

8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)

35 kAIC @480V (UL)

10 kAIC Icu @125 Vdc

20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)

30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)

55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)

10 kAIC Icu @250 Vdc

25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)

65 kAIC @240V (UL)

Resources

3D CAD drawing package

[Eaton Power Defense PDG23G0060TFFL 3D drawing](#)

Application notes

[Consulting application guide - molded case circuit breakers](#)

Brochures

[Power Defense brochure](#)

[Power Defense technical selling booklet](#)

[Power Defense molded case circuit breaker selection poster](#)

[Power Defense molded case circuit breakers - Frame 2 product aid](#)

Catalogs

[Molded case circuit breakers catalog](#)

Certification reports

[PDG4 CCC certification](#)

[PDG4 CB report](#)

[Power Defense Declaration concerning California's Proposition 65](#)

[EU Declaration of Conformity - Power Defense molded case circuit breakers](#)

[PDG2 CB report](#)

Installation instructions

[Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions- IL012239EN H01](#)

[Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN](#)

[Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions – IL012316EN](#)

[Power Defense Frame 2 shunt trip UVR instructions - IL012130EN](#)

[Power Defense Frame 2 locking devices and handle block instructions - IL012149EN](#)

[Power Defense Frame 2 clamp terminal \(steel\), 20A, 3 pole instructions - IL012246EN H03](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 150A, 3 pole instructions - IL012238EN H03](#)

[Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN](#)

[Power Defense Frame 2 Direct Rotary Handle Assy With Interlock Version Instructions \(IL012138EN\).pdf](#)

[Power Defense Frame 2 multi wire connector kit - PDG2X3\(2\)\(4\)TA2253W instructions - IL012243EN H01](#)

[Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN](#)

[Power Defense Frame 2 box terminal \(aluminum\), 225A, 3 pole instructions - IL012235EN H03](#)

[Power Defense Frame 2 PDG2 and PDC\(E\)9 breaker instructions - IL012106EN](#)

[Power Defense Frame 2 screw terminal_end cap kit, 225A, 3 pole instructions - IL012258EN H01](#)

[Power Defense Frame 2 terminal kit - PDG2X3\(2\)\(4\)TA225RF](#)

[instructions - IL012245EN H01](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 50A, 3 pole](#)

[instructions - IL012236EN H03](#)

[Power Defense Frame 2 terminal kit - PDG2X3\(2\)\(4\)TA150RF](#)

[instructions - IL012244EN H01](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 100A, 3 pole](#)

[instructions - IL012237EN H03](#)

[Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA
Handle Attachment Instructions \(IL012260EN\).pdf](#)

[Power Defense Frame 2 handle mech direct rotary handle instructions -
IL012134EN](#)

[Power Defense Frame 2 box terminal \(steel\), 100A, 3 pole instructions -
IL012234EN H03](#)

[Power Defense Frame 2 multi wire connector kit -
PDG2X3\(2\)\(4\)TA2256W instructions - IL012242EN H01](#)

Installation videos

[Power Defense Frame 2 withTMTU, Shunt Trip_UVR Animated
Instructions.rh](#)

[Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated
Instructions.rh](#)

[Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle
Animated Instructions.rh](#)

[Power Defense Frame 2 Locking Devices and Handle Block Animated
Instructions.pdf.rh](#)

[Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh](#)

Multimedia

[Power Defense Frame 2 Direct Rotary Handle Mechanism Installation
How-To Video](#)

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism
Installation How-To Video](#)

[Power Defense Frame 2 Variable Depth Rotary Handle Mechanism
Installation How-To Video](#)

[Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video](#)

[Power Defense Breakers](#)

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Power Defense molded case circuit breakers](#)

[Eaton Power Defense for superior arc flash safety](#)

Specifications and datasheets

[Eaton Specification Sheet - PDG23G0060TFFL](#)

[Time/current curves](#)

Power Defense time current curve Frame 2 - PD2

White papers

Intelligent circuit protection yields space savings

Single and double break MCCB performance revisited

Making a better machine

Molded case and low-voltage power circuit breaker health

Safer by design: arc energy reduction techniques

Molded case and low-voltage breaker health



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia