

Eaton PDG23M0040TFFL

Catalog Number: PDG23M0040TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 40A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

Photo is representative



General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Power Defense molded case circuit breaker | PDG23M0040TFFL |
| | UPC |
| | 786679862049 |
| Product Length/Depth | Product Height |
| 88.9 mm | 152.4 mm |
| Product Width | Product Weight |
| 104.6 mm | 1.81890541 kg |
| Warranty | Compliances |
| Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Certifications |
| | UL 489 |
| | CCC Marked |
| | CSA |
| | IEC 60947-2 |

Delivery program

Amperage Rating

40 A

Circuit breaker frame type

Complete breaker

Frame

2

Number of poles

Three-pole

General information

Circuit breaker type

PD2 Global

Class

Class A

Trip Type

T298

Technical data - Electrical

Voltage rating

600 Vac

Voltage rating - max

600 V

Technical data - Mechanical - Terminals

Terminals

Standard Terminals Load Only

Technical information

Interrupt rating

65 kAIC at 480 Vac

Interrupt rating range

22 kAIC Icu @250 Vdc

100 kAIC @240V (UL)

50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)

65 kAIC @480V (UL)

70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)

35 kAIC @600V (UL/CSA)

100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)

30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)

50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC)

10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)

22 kAIC Icu @125 Vdc

Resources

3D CAD drawing package

[Eaton Power Defense PDG23M0040TFFL 3D drawing](#)

Application notes

[Consulting application guide - molded case circuit breakers](#)

Brochures

[Power Defense technical selling booklet](#)

Power Defense molded case circuit breaker selection poster

Power Defense brochure

Brochures

Power Defense molded case circuit breakers - Frame 2 product aid

Catalogs

Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2

Certification reports

PDG4 CCC certification

EU Declaration of Conformity - Power Defense molded case circuit breakers

PDG4 CB report

Power Defense Declaration concerning California's Proposition 65

PDG2 CB report

Installation instructions

Power Defense Frame 2 tunnel terminal (aluminum), 150A, 3 pole instructions - IL012238EN H03

Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions- IL012239EN H01

Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions – IL012316EN

Power Defense Frame 2 locking devices and handle block instructions - IL012149EN

Power Defense Frame 2 clamp terminal (steel), 20A, 3 pole instructions - IL012246EN H03

Power Defense Frame 2 Direct Rotary Handle Assy With Interlock Version Instructions (IL012138EN).pdf

Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2253W instructions - IL012243EN H01

Power Defense Frame 2 box terminal (aluminum), 225A, 3 pole instructions - IL012235EN H03

Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions - IL012106EN

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN

Power Defense Frame 2 motor circuit protector (HMCP) - IL012326EN

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01

Power Defense Frame 2 screw terminal_end cap kit, 225A, 3 pole

instructions - IL012258EN H01

Power Defense Frame 2 shunt trip UVR instructions - IL012130EN

Power Defense Frame 2 handle mech direct rotary handle instructions - IL012134EN

Power Defense Frame 2 box terminal (steel), 100A, 3 pole instructions - IL012234EN H03

Power Defense Frame 2 tunnel terminal (aluminum), 50A, 3 pole instructions - IL012236EN H03

Power Defense Frame 2 tunnel terminal (aluminum), 100A, 3 pole instructions - IL012237EN H03

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf

Installation videos

Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh

Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh

Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh

Power Defense Frame 2 withTMTU, Shunt Trip_UVR Animated Instructions.rh

Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh

Multimedia

Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video

Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video

Power Defense Frame 5 Trip Unit How-To Video

Power Defense Breakers

Power Defense molded case circuit breakers

Power Defense Frame 6 Trip Unit How-To Video

Eaton Power Defense for superior arc flash safety

Specifications and datasheets

Eaton Specification Sheet - PDG23M0040TFFL

Time/current curves

Power Defense time current curve Frame 2 - PD2

Power Defense time current curves MCP Motor Circuit Protection – PD1, PD2, PD3

White papers

Intelligent circuit protection yields space savings

Single and double break MCCB performance revisited

Molded case and low-voltage power circuit breaker health

Making a better machine

Safer by design: arc energy reduction techniques

Molded case and low-voltage breaker health



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton PDG23M0040TFFL

Catalog Number: PDG23M0040TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 40A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

Photo is representative



General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Power Defense molded case circuit breaker | PDG23M0040TFFL |
| | UPC |
| | 786679862049 |
| Product Length/Depth | Product Height |
| 88.9 mm | 152.4 mm |
| Product Width | Product Weight |
| 104.6 mm | 1.81890541 kg |
| Warranty | Compliances |
| Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Certifications |
| | UL 489 |
| | CCC Marked |
| | CSA |
| | IEC 60947-2 |

Delivery program

Amperage Rating

40 A

Circuit breaker frame type

Complete breaker

Frame

2

Number of poles

Three-pole

General information

Circuit breaker type

PD2 Global

Class

Class A

Trip Type

T298

Technical data - Electrical

Voltage rating

600 Vac

Voltage rating - max

600 V

Technical data - Mechanical - Terminals

Terminals

Standard Terminals Load Only

Technical information

Interrupt rating

65 kAIC at 480 Vac

Interrupt rating range

22 kAIC Icu @250 Vdc

100 kAIC @240V (UL)

50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)

65 kAIC @480V (UL)

70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)

35 kAIC @600V (UL/CSA)

100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)

30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)

50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC)

10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)

22 kAIC Icu @125 Vdc

Resources

3D CAD drawing package

[Eaton Power Defense PDG23M0040TFFL 3D drawing](#)

Application notes

[Consulting application guide - molded case circuit breakers](#)

Brochures

[Power Defense technical selling booklet](#)

Power Defense molded case circuit breaker selection poster

Power Defense brochure

Brochures

Power Defense molded case circuit breakers - Frame 2 product aid

Catalogs

Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2

Certification reports

PDG4 CCC certification

EU Declaration of Conformity - Power Defense molded case circuit breakers

PDG4 CB report

Power Defense Declaration concerning California's Proposition 65

PDG2 CB report

Installation instructions

Power Defense Frame 2 tunnel terminal (aluminum), 150A, 3 pole instructions - IL012238EN H03

Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions- IL012239EN H01

Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions – IL012316EN

Power Defense Frame 2 locking devices and handle block instructions - IL012149EN

Power Defense Frame 2 clamp terminal (steel), 20A, 3 pole instructions - IL012246EN H03

Power Defense Frame 2 Direct Rotary Handle Assy With Interlock Version Instructions (IL012138EN).pdf

Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2253W instructions - IL012243EN H01

Power Defense Frame 2 box terminal (aluminum), 225A, 3 pole instructions - IL012235EN H03

Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions - IL012106EN

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN

Power Defense Frame 2 motor circuit protector (HMCP) - IL012326EN

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01

Power Defense Frame 2 screw terminal_end cap kit, 225A, 3 pole

instructions - IL012258EN H01

Power Defense Frame 2 shunt trip UVR instructions - IL012130EN

Power Defense Frame 2 handle mech direct rotary handle instructions - IL012134EN

Power Defense Frame 2 box terminal (steel), 100A, 3 pole instructions - IL012234EN H03

Power Defense Frame 2 tunnel terminal (aluminum), 50A, 3 pole instructions - IL012236EN H03

Power Defense Frame 2 tunnel terminal (aluminum), 100A, 3 pole instructions - IL012237EN H03

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf

Installation videos

Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh

Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh

Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh

Power Defense Frame 2 withTMTU, Shunt Trip_UVR Animated Instructions.rh

Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh

Multimedia

Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video

Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video

Power Defense Frame 5 Trip Unit How-To Video

Power Defense Breakers

Power Defense molded case circuit breakers

Power Defense Frame 6 Trip Unit How-To Video

Eaton Power Defense for superior arc flash safety

Specifications and datasheets

Eaton Specification Sheet - PDG23M0040TFFL

Time/current curves

Power Defense time current curve Frame 2 - PD2

Power Defense time current curves MCP Motor Circuit Protection – PD1, PD2, PD3

White papers

Intelligent circuit protection yields space savings

Single and double break MCCB performance revisited

Molded case and low-voltage power circuit breaker health

Making a better machine

Safer by design: arc energy reduction techniques

Molded case and low-voltage breaker health



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)