

Specifications

Photo is representative

Eaton PDG23M0060TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 60A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

General specifications

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23M0060TFFL
UPC	786679862476
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 IEC 60947-2 CCC Marked CSA

Delivery program

AMPERAGE RATING	60 A
CIRCUIT BREAKER FRAME TYPE	Complete breaker
FRAME	2
NUMBER OF POLES	Three-pole

Technical data - Electrical

VOLTAGE RATING	600 Vac
-----------------------	---------

Technical information

INTERRUPT RATING	65 kAIC at 480 Vac
INTERRUPT RATING RANGE	10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC) 100 kAIC @240V (UL) 50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 22 kAIC Icu @125 Vdc 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC) 22 kAIC Icu @250 Vdc 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 65 kAIC @480V (UL) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 35 kAIC @600V (UL/CSA)

General information

CIRCUIT BREAKER TYPE	PD2 Global
CLASS	Class A
TRIP TYPE	T298

Technical data - Mechanical - Terminals

TERMINALS	Standard Terminals Load Only
------------------	------------------------------

Resources

3D CAD DRAWING PACKAGE	Eaton Power Defense PDG23M0060TFFL 3D drawing
APPLICATION NOTES	Consulting application guide - molded case circuit breakers Power Defense molded case circuit breaker selection poster Power Defense brochure
BROCHURES	Power Defense technical selling booklet Power Defense molded case circuit breakers - Frame 2 product aid
CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2 Power Defense Declaration concerning California's Proposition 65 PDG2 CB report
CERTIFICATION REPORTS	PDG4 CB report PDG4 CCC certification EU Declaration of Conformity - Power Defense molded case circuit breakers

**INSTALLATION
INSTRUCTIONS**

[Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN](#)

[Power Defense Frame 2 multi wire connector kit - PDG2X3\(2\)\(4\)TA2253W instructions - IL012243EN H01](#)

[Power Defense Frame 2 box terminal \(aluminum\), 225A, 3 pole instructions - IL012235EN H03](#)

[Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN](#)

[Power Defense Frame 2 clamp terminal \(steel\), 20A, 3 pole instructions - IL012246EN H03](#)

[Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions - IL012316EN](#)

[Power Defense Frame 2 shunt trip UVR instructions - IL012130EN](#)

[Power Defense Frame 2 locking devices and handle block instructions - IL012149EN](#)

[Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions- IL012239EN H01](#)

[Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN](#)

[Power Defense Frame 2 handle mech direct rotary handle instructions - IL012134EN](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 150A, 3 pole instructions - IL012238EN H03](#)

[Power Defense Frame 2
box terminal \(steel\), 100A,
3 pole instructions -
IL012234EN H03](#)

[Power Defense Frame 2
Direct Rotary Handle Assy
With Interlock Version
Instructions
\(IL012138EN\).pdf](#)

[Power Defense Frame 2
PDG2 and PDC\(E\)9 breaker
instructions - IL012106EN](#)

[Power Defense Frame 2
tunnel terminal
\(aluminum\), 50A, 3 pole
instructions - IL012236EN
H03](#)

[Power Defense Frame 2
tunnel terminal
\(aluminum\), 100A, 3 pole
instructions - IL012237EN
H03](#)

[Power Defense Frame 2
multi wire connector kit -
PDG2X3\(2\)\(4\)TA2256W
instructions - IL012242EN
H01](#)

[Power Defense Frame 2
terminal kit -
PDG2X3\(2\)\(4\)TA150RF
instructions - IL012244EN
H01](#)

[Power Defense Frame 2
motor circuit protector
\(HMCP\) - IL012326EN](#)

[Power Defense Frame 1
IEC and Frame 2 Rotary
Mechanism with NFPA
Handle Attachment
Instructions
\(IL012260EN\).pdf](#)

[Power Defense Frame 2
screw terminal end cap
kit, 225A, 3 pole
instructions - IL012258EN
H01](#)

	Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01
	Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh
	Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh
INSTALLATION VIDEOS	Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh
	Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh
	Power Defense Frame 2 withTMTU, Shunt Trip UVR Animated Instructions.rh
	Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video
	Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video
	Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video
MULTIMEDIA	Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video
	Power Defense Breakers
	Power Defense molded case circuit breakers
	Power Defense Frame 6 Trip Unit How-To Video
	Power Defense Frame 5 Trip Unit How-To Video

	Eaton Power Defense for superior arc flash safety
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PDG23M0060TFFL
TIME/CURRENT CURVES	Power Defense time current curve Frame 2 - PD2 Power Defense time current curves MCP Motor Circuit Protection – PD1, PD2, PD3
WHITE PAPERS	Making a better machine Molded case and low-voltage power circuit breaker health Single and double break MCCB performance revisited Intelligent circuit protection yields space savings Molded case and low-voltage breaker health Safer by design: arc energy reduction techniques

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

