

# Eaton PDG33M0600MSAN

Catalog Number: PDG33M0600MSAN

Eaton Power Defense motor protection circuit breaker, Globally Rated, Frame 3, Three Pole, 600A, 65kA/480V, Motor protection, Standard Calibration, Adjustable, No Terminals

Photo is representative



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Power Defense motor protection circuit breaker	PDG33M0600MSAN
	UPC
	786679550533
<b>Product Length/Depth</b>	<b>Product Height</b>
109.1 mm	257.1 mm
<b>Product Width</b>	<b>Product Weight</b>
138.9 mm	5.61 kg
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	IEC 60947-2
	CCC Marked
	UL 489
	CSA

## Delivery program

### Amperage Rating

600 A

### Frame

3

### Number of poles

Three-pole

## General information

### Circuit breaker type

PD3 Global

### Class

Class A

## Technical data - Electrical

### Voltage rating

600 Vac

## Technical data - Mechanical

### Switch off technique

Thermomagnetic

## Technical data - Mechanical - Terminals

### Terminals

No Terminals

## Technical information

### Interrupt rating

65 kAIC at 480 Vac

### Interrupt rating range

22 kAIC Icu at 250 Vdc

100 kAIC at 240 V (UL)

## Resources

### 3D CAD drawing package

[Eaton Power Defense MCCB PDG33M0600MSAN 3D drawing](#)

### Application notes

[Consulting application guide - molded case circuit breakers](#)

### Brochures

[StrandAble terminals product aid](#)

[Power Defense brochure](#)

[Power Defense molded case circuit breaker selection poster](#)

[Power Defense technical selling booklet](#)

### Catalogs

[Molded case circuit breakers catalog](#)

### Certification reports

[PDG3 UL authorization 100-400a](#)

[PDG3 UL authorization 250-600a TMTU](#)

[PDG3 45-400A CB report](#)

[PDG3 CSA certification 100-400a](#)

[PDG3B 450A-600A CB report](#)

[EU Declaration of Conformity - Power Defense molded case circuit breakers](#)

[PDG3 CSA certification 250-600a](#)

## Installation instructions

Power Defense Frame 3 terminal kit Cat Num PDG3X3(2)(4)TA400RF instructions - IL012251EN

Power Defense Frame 3 finger protection assembly installation instructions - IL012279EN

Power Defense Frame 3 trip unit replacement instructions - IL012157EN

Power Defense Frame 3 box terminal installation instructions - IL012299EN

Power Defense Frame 3 multi wire connector kit - PDG3X3(2)(4)TA4006W and PDG3X3(2)(4)TA4003W instructions- IL012247EN H01

Power Defense Frame 3 terminal cover assembly instructions - IL012281EN

Power Defense Frame 4 locking devices and handle block instructions - IL012151EN

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN

Power Defense Frame 3 reverse feed connector kit Cat Num PDG3X3(2)(4)TA400HRF instructions - IL012252EN

Power Defense Frame 3 reverse feed connector kit Cat Num PDG3X3(2)(4)TA630RF instructions - IL012253EN

Power Defense Frame 3 extendable shaft rotary handle mech - IL012112EN

Power Defense Frame 3 interphase barrier - IL012229EN H03

Power Defense Frame 3 Aux, Alarm, ST and UVR Animated Instructions.rh

Power Defense Frame 3 rear connection installation instructions - IL012300EN

Power Defense Frame 3 interphase barriers 3-pole - IL012229EN H01

Power Defense Frame 3 shunt trip UVR instructions - IL012140EN

Power Defense Frame 3 locking devices and handle block instructions - IL012150EN

Power Defense Frame 3 Breaker Instructions (IL012107EN).pdf

Power Defense Frame 4 shunt trip UVR instructions - IL012129EN

Power Defense Frame 3 adapter kit installation instructions LZM3 to PD3 - IL012227EN

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions – IL012316EN

Power Defense Frame 3 Direct Rotary Handle Assy With Interlock Version Instructions (IL012139EN).pdf

Power Defense Frame 3 screw terminal end cap kit 600A, 3 pole - IL012264EN

Power Defense Frame 3 screw terminal\_end cap kit, 400A, 3 pole –

[IL012262EN](#)

[Power Defense Frame 3 terminal spreader assembly instructions - IL012301EN](#)

[Power Defense Frame 3 multi-tap terminal kit Cat Num PDG3X3\(2\)\(4\)TA6006W Instructions - IL012248EN](#)

[Power Defense Frame 4 reverse feed connector kit instructions for PDG4X3\(2\)\(4\)TA800RF instructions - IL012254EN](#)

[Power Defense Frame 3 handle mech direct rotary handle instructions - IL012111EN](#)

[Power Defense Frame 3 plug-in adapter installation instructions - IL012311EN](#)

[Power Defense Frame 3 multi-tap terminal kit Cat Num PDG3X3\(2\)\(4\)TA6006WSW instructions - IL012250EN](#)

### **Installation videos**

[Power Defense Frame 3 Locking Devices and Handle Block Animated Instructions.pdf.rh](#)

[Power Defense Frame 3 trip unit replacement animated instructions.rh](#)

[Power Defense Frame 3 Handle Mech Direct Rotary Handle Animated Instructions.rh](#)

[Power Defense Frame 3 Shunt Trip\\_UVR Animated Instructions.pdf.rh](#)

[Power Defense Frame 3 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh](#)

### **Multimedia**

[Power Defense Frame 3 Direct Rotary Handle Mechanism Installation How-To Video](#)

[Power Defense Frame 3 Trip Unit Installation How-To Video](#)

[Power Defense Frame 3 Aux, Alarm, Shunt Trip, and UVR How-To Video](#)

[Eaton Power Defense for superior arc flash safety](#)

[Power Defense molded case circuit breakers](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

[Power Defense Breakers](#)

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

### **Specifications and datasheets**

[Eaton Specification Sheet - PDG33M0600MSAN](#)

### **Time/current curves**

[Power Defense time current curve Frame 3 - PD3](#)

[Power Defense time current curves MCP Motor Circuit Protection – PD1,](#)

PD2, PD3

### White papers

Molded case and low-voltage power circuit breaker health

Making a better machine

Single and double break MCCB performance revisited

Implementation of arc flash mitigating solutions at industrial manufacturing facilities

Intelligent circuit protection yields space savings

Intelligent power starts with accurate, actionable data

Molded case and low-voltage breaker health

Safer by design: arc energy reduction techniques



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)