



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



PFME30LCYUNV3466 Indust-Pfme Led Flood 30000 Lumen 200-480 Vac *Crouse-Hinds*

Catalog Number	PFME30LCYUNV3466
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Pfme Led Floodlight, Cool White, Dimmable Driver, 750W-1000W Hid Equivalent, 50/60 HZ, Polycarbonate Lens, 30000 Lumens, 127 LM/W, Aluminum, Yoke Mount, Standard 120° Angle, > 0.90 PF, 277-480 Vac, 242W
Weight per unit	77.0 (lbs/each)
Product Category	Lighting

Features

dimensions	20.1600 IN X 4.1700 IN X 12.5000 IN
------------	-------------------------------------

Descriptions

Description	INDUST-PFME LED FLOOD 30000 LUMEN 200-480 VAC
extra long description	CRS-H PFME30LCY-UNV34-66 PFME30LCY-
Features	PFME LED floodlights are certified for use wet locations and are UL Listed and CSA certified. These floodlights are suitable for locations requiring continuous and consistent light levels in extreme ambient temperatures and where wet, dusty, hot and/or cold conditions exist.
Long Description	Eaton Crouse-Hinds series PFME LED floodlight, Cool white, Dimmable driver, 750W-1000W HID equivalent, 50/60 Hz, Polycarbonate lens, 30000 lumens, 127 lm/W, Aluminum, Yoke mount, Standard 120° angle, > 0.90 PF, 277-480 Vac, 242W
Product Type	PFME30LCY-UNV34-66

Manufacturer Information

Brand	Eaton
GTIN	00662276966833
Manufacturers Part Number	PFME30LCY-UNV34-66
UPC	662276966833

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	77

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Lighting and Lighting Controls
-------------	-----------------------------------------------------------------------