



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH150PG CNTL 150VA 120X240-12X24

Hammond Power Solutions

Catalog Number	PH150PG
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 120X240 PV, 12X24 SV, 150va
Weight per unit	N/A
Product Category	Encapsulated Industrial Contro

Features

Wattage	150
---------	-----

Dimensions and Weight

Height	3.81
Length	4.94
Width	4

Descriptions

Description	CNTL 150VA 120X240-12X24
extra long description	HMND PH150PG CNTL 150VA 120x240-12x
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 120x240 PV, 12x24 SV, 150VA
Product Type	CNTL 150VA 120X240-12X24
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	HPS
GTIN	00803423078157
Manufacturers Part Number	PH150PG
UPC	803423078157

Taxonomies, Classifications, and Categories

Type	Tranformer > Dry Type > Control > Molded
------	--

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum