



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **PH75MQMJFK 1PH 75VA 240X480V-120X240V 50/60HZ Cu** *Hammond Power Solutions*

Catalog Number	PH75MQMJFK
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 75 Kva, Primary and Secondary Fuse Clips Included
Weight per unit	3.5 (lbs/each)
Product Category	Encapsulated Industrial Contro

### **Features**

Wattage	75
---------	----

### **Descriptions**

Description	1PH 75VA 240X480V-120X240V 50/60HZ CU
extra long description	HMND PH75MQMJ-FK CNTL75 VA240/480
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 75 kVA, Primary And Secondary Fuse Clips Included
Product Type	CNTL75 VA240/480120x240fuse
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

### **Manufacturer Information**

Brand	HPS Imperator®
GTIN	00803423081768
Manufacturers Part Number	PH75MQMJ-FK
UPC	803423081768

### **Taxonomies, Classifications, and Categories**

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

### **Packaging**

Carton	1
Weight Per each	3.54



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum