



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PLT2SM 7.4" Nat Nyl CBL Tie *Panduit Corporation*

Catalog Number	PLT2SM
Manufacturer	Panduit Corporation
Description	Panduit PLT2S-M Locking Cable Ties Are Designed to Satisfy The Needs Of General Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Standard Cross Section, 7.4" (188MM) Length. For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 1000.
Weight per unit	0.0030 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	50

### Dimensions and Weight

Length	7.4
Thickness	0.06

### Descriptions

Description	7.4" NAT NYL CBL TIE
extra long description	PAN PLT2S-M Pan-Ty® PLT2S-M Cable T
Long Description	Panduit PLT2S-M Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Standard cross section, 7.4" (188mm) length. For indoor use, made of Nylon 6.6, are natural in color and come in packages of 1000.
Product Type	Pan-Ty® PLT2S-M Cable Tie, PA6.6, 7.4"L, 50LB, PK1000
Special Features	Indoor

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983540785
Manufacturers Part Number	PLT2S-M
UPC	074983540785

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty 1000

## Packaging

Carton 1000

Package 5000

Weight Per each 0.003

## Uses, Certifications, and Standards

standard CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant  
(Type 2S, 21S), RoHS Compliant