



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLT2SM0 7.4" 50LB BLK LCK CBL Tie *Panduit Corporation*

Catalog Number	PLT2SM0
Manufacturer	Panduit Corporation
Description	Panduit PLT2S-M0 Locking Cable Ties Are Designed to Satisfy The Needs Of General Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Standard Cross Section, 7.4" (188MM) Length. For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 1000.
Weight per unit	3.2 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	7.4
Thickness	0.06

Descriptions

Description	7.4" 50LB BLK LCK CBL TIE
extra long description	PAN PLT2S-M0 Pan-Ty® PLT2S-M0 Cable
Long Description	Panduit PLT2S-M0 Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Standard cross section, 7.4" (188mm) length. For Indoor/Outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 1000.
Product Type	Pan-Ty® PLT2S-M0 Cable Tie, Black, Uv PA6.6, 7.4"L, 50LB, PK
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983540792
Manufacturers Part Number	PLT2S-M0
UPC	074983540792

Taxonomies, Classifications, and Categories

Type	Premium Cable Tie
------	-------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 1000

Packaging

Carton 1000

Package 5000

Weight Per each 3.215

Uses, Certifications, and Standards

standard CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant
(Type 2, 21), RoHS Compliant