



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1010LFL Pan-Term® PN10-10LF-L Loo *Panduit Corporation*

Catalog Number	PN1010LFL
Manufacturer	Panduit Corporation
Description	Locking Fork Terminal, Nylon Insulated, 12 - 10 Awg, #10 Stud Size, Standard Package.
Weight per unit	0.2750 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	#10

Material, Color, and Finish

Color	Yellow
Finish	Tin-Plated

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	PAN-TERM® PN10-10LF-L LOO
extra long description	PAN PN10-10LF-L Pan-Term® PN10-10LF
Long Description	Locking Fork Terminal, nylon insulated, 12 - 10 AWG, #10 stud size, standard package.
Product Type	Pan-Term® PN10-10LF-L Loose Piece Forks

Manufacturer Information

Brand	Panduit®
GTIN	00074983800841
Manufacturers Part Number	PN10-10LF-L
UPC	074983800841

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Locking Fork Terminal

Packaging

Carton	50
Package	500
Weight Per each	0.275



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	9/32
standard	UL Listed 587H E52164; CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)