



## INDUSTRIAL EXTRA HEAVY-DUTY SPECIFICATION GRADE SWITCH, IVORY

PS15AC2I | [Pass & Seymour](#)

### FEATURES & BENEFITS

2pole Toggle Switch, Back & Side Wire, 15amp 120/277volt, Ivory

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Toggle  
Duty: Extra Heavy Duty  
Number Of Poles: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

## DIMENSIONS

Depth (US): 1.073"

Height (US): 3.281"

Width (US): 1.320"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

Grade Type: Industrial

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## INDUSTRIAL EXTRA HEAVY-DUTY SPECIFICATION GRADE SWITCH, IVORY

PS15AC2I | [Pass & Seymour](#)

### FEATURES & BENEFITS

2pole Toggle Switch, Back & Side Wire, 15amp 120/277volt, Ivory

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Toggle  
Duty: Extra Heavy Duty  
Number Of Poles: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

## DIMENSIONS

Depth (US): 1.073"

Height (US): 3.281"

Width (US): 1.320"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

Grade Type: Industrial

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

