



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS15AC3 15A 120/277VAC B+S Wire 3W SW BN

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PS15AC3 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 3-Way Toggle Switch, Back and Side-Wire, 15A 120/277V |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| amperage rating | 15 |
| Contact Rating | 15amp, 120/277vac |
| insulation | False |
| Poles | 3-way |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |
| Wattage | 3 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 15A 120/277VAC B+S WIRE 3W SW BN |
| extra long description | P&S PS15AC3 15A 120/277VAC B+S WIRE |
| Long Description | 3-Way Toggle Switch, Back and Side-Wire, 15A 120/277V |
| Product Type | 15A 120/277VAC B+S Wire 3W SW BN |
| Special Features | High strength toggle, heavy duty toggle bumpers, locking support |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007196542 |
| Manufacturers Part Number | PS15AC3 |
| UPC | 785007196542 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.23 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, UL 20 |