



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS40FBBK 400A 600V Cam Type PLG Series 16 BK

Pass & Seymour/Legrand

| | |
|------------------|---------------------------------------------------------------|
| Catalog Number | PS40FBBK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow |
| Weight per unit | 0.7190 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------------------------------------------------------------|
| amperage rating | 400 |
| Cord Type | Individual conductor, Type SC, SCE, SCT or W, 75°C, copper wire only |
| Poles | Single Pole |
| Voltage | 600.0 V |
| Voltage Rating | 600 |
| Wire Size | 2/0 - 4/0 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|-----|
| Size | 6.8 |
|------|-----|

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 400A 600V CAM TYPE PLG SERIES 16 BK |
| extra long description | P&S PS40FBBK 400A 600V CAM TYPE PLG |
| Long Description | 400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow |
| Product Type | 400A 600V Cam Type PLG Series 16 BK |
| Special Features | Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim b |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007308150 |
| Manufacturers Part Number | PS40-FBBK |
| UPC | 785007308150 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------------------|
| Category Description | Industrial cord connectors |
| Type | Cam-Type Series 16 In-Line Connector Female |

Trade Size

| | |
|----------|-------|
| Amperage | 400.0 |
|----------|-------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.719 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Application | Commercial/Industrial |
| environmental conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |
| nema rating | NEMA 3R and 4 for indoor applications |
| standard | UL, cCSAus |