
15A, 125V EXTRA-HARD USE HOSPITAL- GRADE PLUG, BLACK & CLEAR

PS5266XHG | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Hospital Grade Plug, double pole and three wire, unit arrives completely ready-to-wire, cutting installation time significantly. Its nylon housing provides impact and chemical resistance. Its rugged two-piece cord grip provides more uniform cord retention and the internal dust shield keeps terminals free of contaminants. 15amp 125volt.



- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Black

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: Yes
UL Listing No: No
UN SPSC: 39121402
UR: No

DIMENSIONS

Depth (US): 1.752"

Height (US): 1.516"

Width (US): 1.516"

TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



15A, 125V EXTRA-HARD USE HOSPITAL- GRADE PLUG, BLACK & CLEAR

PS5266XHG | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Hospital Grade Plug, double pole and three wire, unit arrives completely ready-to-wire, cutting installation time significantly. Its nylon housing provides impact and chemical resistance. Its rugged two-piece cord grip provides more uniform cord retention and the internal dust shield keeps terminals free of contaminants. 15amp 125volt.



- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Black

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: Yes

UL Listing No: No

UN SPSC: 39121402

UR: No

DIMENSIONS

Depth (US): 1.752"

Height (US): 1.516"

Width (US): 1.516"

TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

