



NON-FUSIBLE MECHANICAL INTERLOCK

PS530MIR7W | [Pass & Seymour](#)

FEATURES & BENEFITS

Four pole, Five wire, Non-Fusible Mechanical Interlock. 30 amp, 3ØY, 277/480 vac.

- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve Non-Fusible Mechanical Interlock Receptacle

Number Of Poles: 4

Number Of Wires: 5

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

UL Listing No: E31169

UL Standard: Yes

UN SPSC: 39121403

TECHNICAL INFORMATION

Amps: 30A

Volts: 3ØY 277/480VAC

Volts (AC): 277/480

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant



