



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS5366X Straight Blade Plug 3W 20A 125V B&W

Pass & Seymour/Legrand

Catalog Number	PS5366X
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Plug, 20 A, 125 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 1.516 In;0.230 to 0.690 In (Cord) Diameter, 2.791 In Length, #18 to #10 Awg Wire Size, Chemical Resistant, Impact Resistant, Corrosion Resistant, 0.165 LB
Weight per unit	0.1629 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
connection	Wire Grounding
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125

Dimensions and Weight

Size	2.8 in
------	--------

Descriptions

Description	STR BLD PLUG 3W 20A 125V B&W
extra long description	P&S PS5366X STR BLD PLUG 3W 20A 125

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007237009
Manufacturers Part Number	PS5366X
UPC	785007237009

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Straight Blade

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	50
Weight Per each	0.1629

Uses, Certifications, and Standards

Application	Extra Hard Use
standard	FEDSPEC, CULUS, UL 498