



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS5369XHG Straight Blade Conn 3W 20A 125V HG

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | PS5369XHG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Connector 2-Pole 3-Wire 20A 125V Hospital Grade |
| Weight per unit | 0.1810 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|-------------|
| amperage rating | 20 |
| Material | Nylon |
| Number of Wires | 3.0 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 18 - 10 AWG |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|----|
| Size | 3" |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | STRAIGHT BLADE CONN 3W 20A 125V HG |
| extra long description | P&S PS5369XHG STR BLD CONN 3W 20A 1 |
| Long Description | Straight Blade Connector 2-Pole 3-Wire 20A 125V Hospital Grade |
| Product Type | STR BLD Conn 3W 20A 125V HG |
| Special Features | Hospital grade, nylon housing, rugged 2 piece cord grip, tri-drive assembly screws |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007236804 |
| Manufacturers Part Number | PS5369-XHG |
| UPC | 785007236804 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Straight Blade |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.181 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------|
| Application | Commercial |
| nema rating | 5-20R |
| standard | FEDSPEC, CULUS, UL 498, FEDSPEC |