

Eaton PSG480F24RM

Catalog Number: PSG480F24RM

Eaton PSG power supply, Aluminum, 400-500 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 960W output power, -25°C-80°C operating temp



Photo is representative

General specifications

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG480F24RM
	UPC
	786685683607
Product Length/Depth	Product Height
7 in	7 in
Product Width	Product Weight
6 in	3.9 lb
Warranty	Compliances
3 year	RoHS Compliant
	CE Marked

Certifications

UL 508
EN Listed
CSA Std. C22.2
IEC Rated

Operating temperature - max

80 °C

Operating temperature - min

-25 °C

Phase

Three-phase

Frequency rating

47-63 Hz

Enclosure color

Aluminum

Output voltage

24 V

Terminals

Finger-safe

Input voltage

400-500 Vac

Output

960 W

Brochures

Eaton's PSG Series Power Supplies

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Drawings

PSG480F24RM 2D PDF

PSG480F24RM AutoCAD 2D Footprint (mm)

PSG480F24RM 2D Drawing Xchange

PSG480F24RM AutoCAD 2D Footprint

PSG480F24RM 3D Inventor

PSG480F24RM 3D Model Xchange

Installation instructions

Installation Instructions for PSG480F Power Supply

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - PSG480F24RM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia