



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT2097BK Self Test Plugtail Gfci Recp 20A BK

Pass & Seymour/Legrand

Catalog Number	PT2097BK
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 20 A, 125 V, 2 Poles, #12 Awg Compatible Wire Size, Control Circuit Actuator, Built-In Connector Connection, 60 HZ, 1.72 In Length, 4.20 In Height, Thermoplastic Material, Black, 0.025 Sec Trip Time, Impact Resistant, 0.2500 LB
Weight per unit	0.2450 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Built-in Connector
interrupt rating	4 to 6 mA
media	Yes
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Width	1.73
-------	------

Descriptions

Description	SELF TEST PLUGTAIL GFCI RECP 20A BK
extra long description	P&S PT2097BK SELF TEST PLUGTAIL GFC

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007048186
UPC	785007048186

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	PLUGTAIL® Specification Grade 20A Self-Test Duplex GFCI

Packaging

Carton	1
Package	10
Weight Per each	0.245

Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL