



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT2097HGRED Self Test Plugtail Gfci Recp Hosp GRD 20A RD

Pass & Seymour/Legrand

Catalog Number	PT2097HGRED
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Plugtail Self Test Hospital Grade Gfci Red
Weight per unit	0.2450 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Built-in Connector
interrupt rating	4 to 6 mA
Material	Thermoplastic
media	Yes
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73

Descriptions

Description	SELF TEST PLUGTAIL GFCI RECP HOSP GRD 20A RD
extra long description	P&S PT2097HGRED SELF TEST PTAIL GFC
Long Description	20A 125V Plugtail Self Test Hospital Grade GFCI Red
Product Type	Self Test Ptail Gfci HG Rec 20A Red
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007048919
Manufacturers Part Number	PT2097-HGRED
UPC	785007048919



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	PLUGTAIL® Hospital Grade Tamper-Resistant 20A Self-Test GFCI Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.245

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL