

# PlugTail™ Single Pole 20 amp Toggle Switch, Ivory

PT20AC1I



PlugTail™ Single Pole Toggle Switch,  
20amp 120/277vac, Ivory

## features & benefits

- Ground wire pre-mounted to the box
- Mud ring factory installed
- 4" square x 1 1/2" or 2 1/8" metal boxes
- PlugTail Right Angle Connectors with 12 AWG copper pigtails
- All Double Gang Kits contain two right angle PlugTail connectors

## specifications

### General Info

Color: Ivory  
Product Series: PlugTail  
Type: Toggle  
Number Of Poles: 1

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
cULus: Yes  
Federal Spec: Yes  
Fed Spec Number: WS896  
UN SPS C: 39121507

### Dimensions

Depth U S: 1.073"  
Height U S: 3.281"  
Width U S: 1.320"

**Technical Information**

Amps: 20 Amp  
Volts: 120/277VAC  
Volts A C: 120/277  
Grade Type: Specification