



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PT5362LA Dup Recept Spec GRD 20A/125V La

*Pass & Seymour/Legrand*

Catalog Number	PT5362LA
Manufacturer	Pass & Seymour/Legrand
Description	Plugtail Spec Grade Duplex Receptacle 20AMP 125VOLT Light Almond
Weight per unit	0.2300 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	12

### Dimensions and Weight

Height	3.281
Width	.625

### Descriptions

Description	DUP RECEPT SPEC GRD 20A/125V LA
extra long description	P&S PT5362LA DUP RECEPT SPEC GRD 20
Long Description	PlugTail Spec Grade Duplex Receptacle 20amp 125volt Light Almond
Product Type	Dup Recept Spec GRD 20A/125V La
Special Features	Plated steel wrap strap design for maximum durability and corrosion resistance. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Three drive screws anchor strap to back body and face. No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. Crimped and welded contacts. Ultrasonically welded polycarbonate connector housing secures termin



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007091700
Manufacturers Part Number	PT5362LA
UPC	785007091700

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.23

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, cULus UL498
Temperature Rating	-40° - 60° C