

# PlugTail™ Spec Grade Receptacles, 20A, 125V, White

PT5362W



PlugTail™ Spec Grade Duplex Receptacle  
20amp 125volt White



## features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Crimped and welded contacts.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

## specifications

**General Info**

Color: white  
Product Series: PlugTail  
Type: Receptacles  
Special Features: split circuit

**Listing Agencies/Third Party Information**

CUL Listing No: UL498  
cULus: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: .625"  
Height U S: 3.281"  
Width U S: 1.5"

**Technical Information**

Amps: 20 Amp  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Federal Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant