



## PLUGTAIL® HEAVY-DUTY COMPACT DESIGN HOSPITAL-GRADE DUPLEX RECEPTACLE, IVORY

PT8300HI | [Pass & Seymour](#)

### FEATURES & BENEFITS

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each hospital-grade receptacle. The connector simply snaps into the back of the device—no fussing with wires, stripping or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now installation is a snap! PlugTail...The toughest and safest hospital-grade receptacles available.

For detailed PlugTail® information, visit our PlugTail Headquarters.



### SPECIFICATIONS

**Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.

**Auto-ground clip** assures positive ground.

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Zinc-plated steel strap** for added strength & ground connectivity.

**Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

**Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger-safe housing environment.

**Pre-stripped connector leads** fasten to conductors, easier than standard pigtailed.

**No exposed terminals** before, during, or after installation increases safety at all phases of product life.

#### GENERAL INFO

Color: Ivory

Available Colors: Gray, Red, White, Black, Light Almond, Brown

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Listed: Yes  
CSA Standard: C22.2 No. 42  
CUL Listing No: E140596  
cUL Standard: Yes  
Federal Spec: Yes  
UL Listing No: E140596  
UL Standard: UL498  
UN SPSC: 3912406

#### **DIMENSIONS**

Depth (US): .625"  
Height (US): 3.281"  
Width (US): 1.5"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20R  
NEMA Rating: Yes  
Volts: 125V

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO





## PLUGTAIL® HEAVY-DUTY COMPACT DESIGN HOSPITAL-GRADE DUPLEX RECEPTACLE, IVORY

PT8300HI | [Pass & Seymour](#)

### FEATURES & BENEFITS

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each hospital-grade receptacle. The connector simply snaps into the back of the device—no fussing with wires, stripping or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now installation is a snap! PlugTail...The toughest and safest hospital-grade receptacles available.

For detailed PlugTail® information, visit our PlugTail Headquarters.



### SPECIFICATIONS

**Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.

**Auto-ground clip** assures positive ground.

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Zinc-plated steel strap** for added strength & ground connectivity.

**Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

**Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger-safe housing environment.

**Pre-stripped connector leads** fasten to conductors, easier than standard pigtailed.

**No exposed terminals** before, during, or after installation increases safety at all phases of product life.

#### GENERAL INFO

Color: Ivory

Available Colors: Gray, Red, White, Black, Light Almond, Brown

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Listed: Yes  
CSA Standard: C22.2 No. 42  
CUL Listing No: E140596  
cUL Standard: Yes  
Federal Spec: Yes  
UL Listing No: E140596  
UL Standard: UL498  
UN SPSC: 3912406

#### **DIMENSIONS**

Depth (US): .625"  
Height (US): 3.281"  
Width (US): 1.5"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20R  
NEMA Rating: Yes  
Volts: 125V

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

