



## PLUGTAIL® CONNECTORS, RIGHT ANGLE, STRANDED, 25"

PTRA6STRB25 | [Pass & Seymour](#)

### FEATURES & BENEFITS

#### PlugTail® Connectors Right Angle Stranded 25"

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Available in any wire length up to 25 inches, use Configurable Solutions to order.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Product Series: PlugTail

Type: connectors

Special Features: right angle, stranded

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UN SPSC: 39121406

#### DIMENSIONS

Length (US): 25"

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

