



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV106LFL 12-10 Vnyl Ins LCKNG FRK Term Ylw # 6 Stud *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PV106LFL |
| Manufacturer | Panduit Corporation |
| Description | Locking Fork Terminal, Vinyl Insulated, Funnel Entry, Butted Seam, 12- 10 Awg, #6 Stud Size, Standard Package. |
| Weight per unit | 0.2400 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| connection | Funnel Entry |
| insulation | Vinyl |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #10 |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Yellow |
| Finish | Tin-Plated |

Dimensions and Weight

| | |
|------|----|
| Size | #6 |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | 12-10 VNYL INS LCKNG FRK TERM YLW # 6 STUD |
| extra long description | PAN PV10-6LF-L Pan-Term® PV10-6LF-L |
| Long Description | Locking Fork Terminal, vinyl insulated, funnel entry, butted seam, 12- 10 AWG, #6 stud size, standard package. |
| Product Type | Pan-Term® PV10-6LF-L Loose Piece Terminal |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983808120 |
| Manufacturers Part Number | PV10-6LF-L |
| UPC | 074983808120 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Weight Per each | 0.24 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Enclosure | Fork shape |
| Mounting | 5/16 |
| standard | UL Listed 587H E52164; CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |