



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV108LFL 12-10 Vnyl Ins LCKNG FRK Term Ylw # 8 Stud *Panduit Corporation*

Catalog Number	PV108LFL
Manufacturer	Panduit Corporation
Description	The PV10-8LF-L Pan-Term® Terminal Is A Vinyl Insulated, Locking Fork Terminal. The Locking Tongue Design Locks In Place For A Secure Connection. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2400 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

### Material, Color, and Finish

Color	Yellow
Finish	Tinned

### Dimensions and Weight

Size	#8
------	----

### Descriptions

Description	12-10 VNYL INS LCKNG FRK TERM YLW # 8 STUD
extra long description	PAN PV10-8LF-L Pan-Term® PV10-8LF-L
Long Description	The PV10-8LF-L Pan-Term® Terminal is a vinyl insulated, locking fork terminal. The locking tongue design locks in place for a secure connection. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV10-8LF-L Fork Terminal, Yellow, Vinyl, 10-12 Awg

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983808144
Manufacturers Part Number	PV10-8LF-L
UPC	074983808144



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Locking Fork Terminal

## Availability

minimum qty ..... 50

## Packaging

Carton ..... 50

Package ..... 500

Weight Per each ..... 0.24

## Uses, Certifications, and Standards

Enclosure ..... Fork shape

Mounting ..... 5/16

standard ..... CSA Certified LR31212;UL Listed 587H E52164

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)