



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV148LFC 18-14 Vnyl Ins LCKNG FRK Term Blue # 8 Stud

Panduit Corporation

Catalog Number	PV148LFC
Manufacturer	Panduit Corporation
Description	The PV14-8LF-C Pan-Term® Terminal Is A Vinyl Insulated, Locking Fork Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.3000 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#14

Material, Color, and Finish

Color	Blue
Finish	Tin-Plated

Dimensions and Weight

Size	#8
------	----

Descriptions

Description	18-14 VNYL INS LCKNG FRK TERM BLUE # 8 STUD
extra long description	PAN PV14-8LF-C Pan-Term® PV14-8LF-C
Long Description	The PV14-8LF-C Pan-Term® Terminal is a vinyl insulated, locking fork terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV14-8LF-C Fork Terminal, Blue, Vinyl, 14-18 Awg,

Manufacturer Information

Brand	PANDUIT
GTIN	00074983808083
Manufacturers Part Number	PV14-8LF-C
UPC	074983808083

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Locking Fork Terminal



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 100

Packaging

Carton 100

Package 500

Weight Per each 0.3

Uses, Certifications, and Standards

Enclosure Fork shape

Mounting 5/16

standard UL Listed 587H E52164; CSA Certified LR31212

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)