



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1810RCY Red, Vinyl, 16-22 Awg, #10 Stud *Panduit Corporation*

Catalog Number	PV1810RCY
Manufacturer	Panduit Corporation
Description	The PV18-10R-Cy Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2800 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#18

Material, Color, and Finish

Color	Red
Finish	Tin-Plated

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	RED, VINYL, 16-22 AWG, #10 STUD
extra long description	PAN PV18-10R-CY Pan-Term® PV18-10R-
Long Description	The PV18-10R-CY Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV18-10R-Cy Ring Terminal, Red, Vinyl, 16-22 Awg,

Manufacturer Information

Brand	PANDUIT
GTIN	00074983688500
Manufacturers Part Number	PV18-10R-CY
UPC	074983688500

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	500
Weight Per each	0.28

Uses, Certifications, and Standards

Enclosure	Ring shape
Mounting	5/16
standard	cULus Listed 587H E52164, CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)