



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV2010CT00 2IN PVC Coated Rigid

Calpipe Industries, Inc

| | |
|------------------|--|
| Catalog Number | PV2010CT00 |
| Manufacturer | Calpipe Industries, Inc |
| Description | Rigid Conduit, Steel Material; Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; 10 Foot; 2.083 Inch Inner Diameter; 2.455 Inch Outer Diameter; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard |
| Weight per unit | N/A |
| Product Category | 20220415171901 |

Features

| | |
|---------------------|-----------------------|
| Applicable Standard | ANSI C80.1, NEMA RN-1 |
| End Style | Threaded |
| Material | Steel |
| Wall Thickness | 0.146 INCH |

Material, Color, and Finish

| | |
|--------|--|
| Finish | Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior |
|--------|--|

Dimensions and Weight

| | |
|----------------|------------|
| Inner Diameter | 2.083 INCH |
| Length | 10 Foot |
| Outer Diameter | 2.455 INCH |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Additional Information | Constructional Feature Corrosion Resistant; Includes Coupling; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mil |
| Commodity Description | Pvc Schedule 40 Conduit |
| Description | 2IN PVC COATED RIGID |
| extra long description | STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 2.083 INCH INNER DIAMETER; 2.455 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 376 POUND PER 100 FOOT WEIGHT; 300 FOOT PER BUNDLE STANDARD PACKAGE; 2 INCH TRADE SIZE; 0.146 INCH WALL THICKNESS; THREADED END STYLE; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; INCLUDES COUPLING; PV MODEL |
| Long Description | RIGID CONDUIT, STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 10 FOOT; 2.083 INCH INNER DIAMETER; 2.455 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD |
| Product Type | Rigid Conduit |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Calpipe Industries, Inc |
| GTIN | 00847656076375 |
| Manufacturers Part Number | PV2010CT00 |
| Model | PV |
| UPC | 847656076375 |

Trade Size

| | |
|------------|--------|
| Trade Size | 2 INCH |
|------------|--------|

Packaging

| | |
|------------------|------------------------|
| Carton | 1 |
| Standard Package | 300 Foot per Bundle |
| Weight | 376 Pound per 100 Foot |
| Weight Per each | 0 |

Uses, Certifications, and Standards

| | |
|----------|-----------|
| Approval | UL 6, CUL |
|----------|-----------|