

Eaton PV4

Catalog Number: PV4

Eaton B-Line series push button enclosures, 7.25" height, 4.75" length, 6.25" width, NEMA 12, Screw cover, PV enclosure, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series push button enclosures	PV4
	UPC
	782051702460
Product Length/Depth	Product Height
4.75 in	7.25 in
Product Width	Product Weight
6.25 in	4 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

PV enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

External mounting feet

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - PV4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)