




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PVC34 SCH 40 3/4" 10' PVC Conduit

Heritage Plastics

Catalog Number	PVC34
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 0.780 In Conduit Inner Diameter, 1.050 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 4400 FT/PK Package Quantity, Belled End;Corrosion Resistant;Rust Resistant;Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 3/4 In Trade Size, 0.113 In Wall Thickness, 0.216 LB Weight
Weight per unit	0.2160 (lbs/each)
Product Category	PVC Conduit, Fittings, & Boxes

Descriptions

Description	SCH 40 3/4" 10' PVC CONDUIT
-------------	-----------------------------

Taxonomies, Classifications, and Categories

Category Description	PVC Schedule 40 Conduit
	Conduit & Raceways - Pvc Conduit, Fittings, & Boxes

Availability

minimum qty	10
-------------	----

Packaging

Carton	100
Package	4400
Weight Per foot	0.216