



GE  
Lighting

**20814 - Q20MR16C/FL40 10**

GE ConstantColor® Precise™ MR16



**GENERAL CHARACTERISTICS**

Lamp Type	Halogen - MR
Bulb	MR16
Base	2-Pin (GX5.3)
Filament	C-6
Rated Life	5000.0 hrs
Lamp Enclosure Type (LET)	Open or enclosed fixtures

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	240.0
Center Beam Candlepower (CBCP)	525.0
Color Temperature	2900.0 K
Beam Spread	40.0 °

**ELECTRICAL CHARACTERISTICS**


Wattage	20.0
Voltage	12.0

**DIMENSIONS**

Maximum Overall Length (MOL)	1.8750 in(47.6 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

**PRODUCT INFORMATION**

Product Code	20814
Description	Q20MR16C/FL40 10
ANSI Code	BAB
Standard Package	BUNDLE
Standard Package GTIN	00043168208147
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168990080



**CAUTIONS & WARNINGS**

**Caution**

- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

**Warning**

- Risk of Burn
  - Allow lamp/fixture to cool before handling.
  - Turn power off before installing lamp.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product-- see instructions.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
  - Do not touch glass with bare hands.
  - Do not use lamp if outer glass is scratched or broken.
  - Use eye protection when handling lamp.
  - Use in enclosed fixture rated for this product.



GE  
Lighting

## 20814 - Q20MR16C/FL40 10

GE ConstantColor® Precise™ MR16



### GENERAL CHARACTERISTICS

Lamp Type	Halogen - MR
Bulb	MR16
Base	2-Pin (GX5.3)
Filament	C-6
Rated Life	5000.0 hrs
Lamp Enclosure Type (LET)	Open or enclosed fixtures

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens	240.0
Center Beam Candlepower (CBCP)	525.0
Color Temperature	2900.0 K
Beam Spread	40.0 °

### ELECTRICAL CHARACTERISTICS


Wattage	20.0
Voltage	12.0

### DIMENSIONS

Maximum Overall Length (MOL)	1.8750 in(47.6 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

### PRODUCT INFORMATION

Product Code	20814
Description	Q20MR16C/FL40 10
ANSI Code	BAB
Standard Package	BUNDLE
Standard Package GTIN	00043168208147
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168990080



### CAUTIONS & WARNINGS

#### Caution

- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

#### Warning

- Risk of Burn
  - Allow lamp/fixture to cool before handling.
  - Turn power off before installing lamp.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product-- see instructions.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
  - Do not touch glass with bare hands.
  - Do not use lamp if outer glass is scratched or broken.
  - Use eye protection when handling lamp.
  - Use in enclosed fixture rated for this product.