

Specifications

Eaton QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB



Photo is representative



General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QB1030GF
UPC	786680222429
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	1 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL 489

Physical Attributes

CIRCUIT BREAKER TYPE	QB
CONNECTION	Bolt-on
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-4 AWG

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - QB1030GF](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

